


Series 165, 166 Retainers



WEIGHT

.48 g/cm (.043 oz/in)

MATERIALS AND FINISH


- Material:**
.41 (.016) thick Beryllium Copper C17510, Temper TF00 per ASTM B534
- Finish:**
See finish table

SPRING RATE

56.0 N/cm (32 lbs/in) of deflection per spring finger

Dash No.	PCB Thickness	B Dimension +0.38 (.015)/-0.0 (.000)	G Dimension +0.0 (.00)/-0.80 (.03)
-06	1.6 (1/16)	1.91 (.075)	1.14 (.045)
-09	2.4 (3/32)	2.67 (.105)	1.91 (.075)

165 Shown, 166 Opposite



Finish Table

Code Letter	Finish
[blank]	165/166: no finish
"T"	Bright Tin plate per Mil-T-10727 .005 (.0002) min.
"N"	Nickel plate per QQ-N-290 Cl. 1, Gr. F
"ZN"	Zinc plate per ASTM-B633 Type III (clear), SC1
"EN"	Electroless nickel plate per Mil-C-26074 Cl. 1 Gr. B

Part Number Code

165 or 166 - 06 - 3.25 - N

PCB Thickness

1.6 (.063) _____ **06**

2.4 (.094) _____ **09**

Length

31.75 (1.25) to 311.15 (12.25) _____ **3.25**

In 25.4 (1.00) increments

Other lengths available on request

Finish

Nickel Plate _____ **N**

Or choose from finish table

Part Number Code Example:

165-06-4.25-T

Series 165 BeCu, with bright tin finish,

107.95 (4.25) long designed for 1.6 (.063) thick printed circuit boards

nVent SCHROFF, Inc.

7328 Trade Street
San Diego, CA 92121 USA
+1 800-525-4682

CALMARK™



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO RAYCHEM SCHROFF