


## Temperature sensor with M16 gland

### PRODUCT OVERVIEW



Raychem MONI-PT100-260/2 temperature sensor is designed for providing accurate temperature measurements.

The MONI-PT100-260/2 sensor exhibits excellent mechanical, electrical and thermal properties what makes the sensor extremely useful for a broad range of applications. The sensor can be connected to the control device using 3-wire technology for providing highest accuracy and measuring stability.

### PRODUCT SPECIFICATIONS

#### Sensor

Type	Pt100 (3 wire) DIN IEC 751, Class B
Jacket/Sheath Material	Extension cable PTFE (Fluoropolymer) Measuring tip stainless steel (316 Ti)
Cable construction	Braided
Measuring range	-50°C to +260°C
Maximum exposure temp. tip	400°C
Length	Total sensor length 2 m (other lengths are available on request) Length of the measuring tip ca 50 mm
Nominal Diameter (OD)	Diameter of the sensor cable 4.8 mm Diameter of the tip 6 mm.
Conductors	4 x 0.5 mm <sup>2</sup> (Red, Red, White and braid) PTFE insulated
Minimum bending radius	Sensor cable minimum 20 mm, the measuring tip should not be bent

#### Cable gland

Thread size (color)	M16 (Black)
Material	Polyamide (PA) Halogen-free
Temperature range	-40°C to +75°C
Cable acceptance size	Suitable for cables from 4 to 9 mm diameter

## APPROVALS

For use in ordinary area.

The sensor can be used in a hazardous area (Zone 1, Zone 2, Zone 21 and Zone 22) in combination with a intrinsically safe barrier or with a temperature controller / thermostat that has intrinsic safe barriers included in its design. (Simple apparatus in accordance with IEC 60079-11)

Cable gland: for use in ordinary and potentially hazardous area Zone 1 and Zone 2 (Gas), Zone 21 and Zone 22 (Dust)

### Temperature classification

Temperature classification is defined by the complete system.

## ORDERING INFORMATION

Part description	Moni-PT100-260/2
PN	1244-006615

### North America

Tel +1 800 545 6258  
info@chemelex.com

### Latin America

Tel +1 713 868 4800  
info@chemelex.com

### Europe, Middle East , Africa, India

Tel +32 16 213 511  
Fax +32 16 213 604  
info@chemelex.com

### Asia Pacific

Tel +86 21 2412 1688  
infoAPAC@chemelex.com



**Raychem Tracer Pyrotenax Nuheat**