

RackChiller In-Row 45

Data Solutions



RackChiller In-Row Coolers (IRC) are designed to deliver localized/supplemental energy efficient cooling in data centers. The RackChiller In-Row 45 air-to liquid cooler is a modular and scalable precision cooling solution that can replace or supplement traditional data center cooling infrastructure. The units can be scaled optimally to suit individual packaging density and redundancy requirements.

The cooling system is integrated into a Varistar CP mobile frame for ideal side by side connection to Varistar CP or third party racks. The cooler comes with perforated front and rear doors. This allows seamless integration into rows of racks with hot or cold aisle containment. The integrated fans move the warm exhaust air from the hot aisle through an air to water heat exchanger where the heat is transferred to a water circuit. The air is then provided into the cold aisle towards the equipment.

DESIGN

In-Row air/liquid cooler, ideal for hot aisle containment

Hot-swappable components simplify repair and maximize availability

Designed for efficient operation at increased facility water temperatures

Combination with direct to chip liquid cooling

Modular standard - easy to adapt to individual requirements.

Minimum changes between In-Row and LHX+ (In-Rack) design - simplifies planning, layout and specification

Fans, power supplies, controller and control valve all are hot-swappable

Automatic fan speed and valve opening control

7" high resolution touch screen interface

Hydraulic and electric connection through top or bottom

Monitoring via Ethernet interface (Web browser, Modbus TCP, SNMP v2c) and Modbus RTU

SPECIFICATIONER

Table 1/2

Katalognummer	Produktyp	Produktfamilj	Bredd	Djup	Höjd	Matningsspänning
10630-102	Värmeväxlare, luft/vätska	Rackkylaggregat	300mm	1000mm	2000mm	200 – 240V
10630-103	Värmeväxlare, luft/vätska	Rackkylaggregat	300mm	1200mm	2000mm	200 – 240V

Table 2/2

Katalognummer	Kylmedelsmatning	Yta	Material	Antal i förpackningen	Kapslingsklass	Rackhöjd
10630-102	Övre	Pulverlackerad	Stål	1	IP20	42U
10630-103	Övre, Underdel	Pulverlackerad	Stål	1	IP20	42U

YTTERLIGARE PRODUKTINFORMATION

For trouble-free operation of the air/liquid heat exchanger the quality requirements of the coolant must be maintained; The selection of appropriate anti-corrosion and frost protection agents depends on the environment in which the unit is used and on the external chiller

At coolant temperatures below 14 °C, there is an increased risk of condensation. We recommend using a condensate management package

WARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial.

Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt stora utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. Alla nVent-märken och -logotyper ägs eller licensieras av nVent Services GmbH eller dess närliggande bolag. Alla andra varumärken tillhör respektive ägare. nVent förbehåller sig rätten att ändra specifikationer utan föregående meddelande.

This document is system-generated.