

nVent ERIFLEX FLEXIBAR avancerad, förtennad

Energiföretag

Efter omfattande forskning är nVent ERIFLEX stolta över att få upprätta en ny guldstandard i termer av isolering för flexibla samlingsskenor under namnet nVent ERIFLEX Flexibar avancerad. The new product is low smoke, halogen-free and flame retardant all while maintaining the level of flexibility and reliability that our partners have come to expect from nVent ERIFLEX Flexibar.

Compared to standard PVC insulation, nVent ERIFLEX Flexibar Advanced does not generate corrosive gases and produces a relatively low smoke opacity in accordance with ISO 5659-2. The low smoke characteristic improves the visibility conditions for people to be able to easily locate the emergency exit and also allows rescue workers to assess an emergency situation more clearly. nVent ERIFLEX Flexibar Advanced means greater safety for individuals, less damage for your electrical equipment and less environmental impact.

The halogen-free feature enables a reduction in the quantity of toxic smoke. nVent ERIFLEX Flexibar Advanced does not contain any halogens, according to IEC 60754-1, minimizing toxicity and making it the ideal product for use in enclosed spaces such as data centers, rail and other spaces where people are welcome such as hospitals and schools. This also facilitates the use of nVent ERIFLEX Flexibar Advanced in specific applications such as submarines, switchboards and other enclosed environments that require a low emissions solution.

In addition to being halogen-free, nVent ERIFLEX Flexibar Advanced is also compliant with the UL 94-V0 testing standard. Andelen flamskydd i testet visar den självsläckande funktionen. This superior feature of nVent ERIFLEX Flexibar Advanced is also shown by the Limiting Oxygen Index (LOI) at 30%. In case of fire, ERIFLEX Flexibar Advanced generates a limited quantity of smoke that is less damaging to your electrical equipment.



CERTIFIERING



FUNKTIONER

Thin layers of tinned electrolytic copper formed into a stack

Full range from 19.5 mm² up to 1200 mm² and 125 A to 2800 A

Insulated by high-resistance, halogen free, flame retardant and low smoke material with less than 20% contact with conductor for high flexibility

Easily bent, folded, and twisted, improving assembly flexibility, shortening connections, and decreasing footprint

Dramatically smaller and more flexible than comparable cable based on ampacity

Better power density than cable with lower skin effect ratio

Connections made by punching and bolting directly through the copper laminates or clamping onto the end of the nVent ERIFLEX Flexibar

No lugs needed, reducing installation time and improving resistance to vibration

Weight savings and material savings compared to wire alternatives

Reduces total installation cost

Traceability codes and designation part numbers printed on insulation

Conforms to NF EN 45545 obtaining an HL3 classification for chapters R22 and R23

100% production dielectric tested

RoHS compliant

Förtätnad koppar möjliggör anslutning av koppar- eller aluminiumledare

On request, can be manufactured with other colors (typically with Orange sleeve for battery connection)

Compliant to ISO 6469-1 (Electrically propelled road vehicles - Part 1: Rechargeable energy storage system) - Section 6.2.2 Vibrations

SPECIFIKATIONER

Table 1/4

Katalognummer	Artikelnummer	Dielektrisk styrka	Halogen Free Rating	Low Smoke Rating	Smoke, Toxicity and Acidity Rating	UV Resistance Rating
FADV2MTC3X9	534001	20	UL® 2885, IEC® 60754-1, IEC® 62821-1	IEC® 61034-2, ISO 5659-2, UL® 2885	IEC® 60754-2	UL® 854, UL® 2556

Table 2/4

Katalognummer	Artikelnummer	Insulation Elongation	Isoleringstjocklek	Max Working Voltage, EN 50264-3-1	Max Working Voltage, UL/CSA/IEC	Arbetstemperatur
FADV2MTC3X9	534001	500	1.8	6000	1000, 1500	-50 to 115

Table 3/4

Katalognummer	Artikelnummer	Certifieringsinformation	ΔT 40 K	ΔT 50 K	ΔT 60 K	Conducting Layers (N)
FADV2MTC3X9	534001	UL® 67, UL® 758	120	134	147	3

Table 4/4

Katalognummer	Artikelnummer	A	B	2 Bar Current Coefficient	3 Bar Current Coefficient
FADV2MTC3X9	534001	9	0.8	1.72	2.25


ADDITIONAL PRODUCT DETAILS

ADMISSIBLE CURRENTS: This table indicates the temperature rise produced by chosen current in the given section. This calculation does not take into account the heat dissipation from the switch gear.

ΔT = Temperature of conductors – Internal temperature of panel.

Refer to technical documentation for additional ampacity ratings.

DIAGRAM



VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE