

CS480 Base Bracket/Wall Flange



CS480 Base Bracket/Wall Flange allows for fixed positioning on a horizontal or vertical surface when rotation is not needed.

BRANCHSTANDARDER

IEC 60529, IP66

DESIGN

Gasket and mounting hardware are included

Surface mounting fasteners are not provided

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPECIFIKATIONER

Table 1/1

Katalognummer	Höjd	Bredd	Djup	Material	Yta	Snabbleverans
CCSS48BB	65mm	109mm	109mm	Rostfritt stål 304	Borstad	Nej

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE