


SpectraCool Slim Fit inomhus luftkonditionering - EMEA

SpectraCool SlimFit Air Conditioners are designed with three space-saving mounting options to maximize footprint. They have been developed to meet the requirements of worldwide industrial customers, easy to specify and easy to use. From filterless operation to global certifications, the SpectraCool Slim Fit Air Conditioner makes automation cooling easy for system designers and operations maintenance teams around the world.

Select units come with a Commboard for Remote Access Control (RAC), an integrated, parametric controller designed to work seamlessly with our enclosure air conditioner units for the purpose of remotely monitoring and managing anywhere from a single unit to an entire network of Spectra cool air conditioners from virtually anywhere in the world with a secure internet connection. Ensure that your systems are always running at optimal temperature levels, increase productivity and improve overall system reliability.



BRANSCHSTANDARDER

UL/cUL Listed Type 12; File No.SA6453

CE, EAC, RoHS

Cooling performance tested by TÜV SÜD Germany, according to DIN EN 14511

IP 54 internal loop, IP 34 external loop

DESIGN

Standardkylenheter är kompatibla med en skåpdörrsbrytare

Slim Fit Design with three mounting options; fully recessed, partial recessed and surface mount

Aesthetic design plastic cover to optimize air flow

R134a refrigerant

Voltage: 230 V (50/60 Hz), 115 V (50/60 Hz) and 400/460 V 3-phase (50/60 Hz)

Operating temperature range from 50 F / 10 C to 131 F / 55 C

Easy filter replacement for extremely dusty environments

Dust resistant coils for filterless operation

Active condensate management to prevent dripping water

Energy efficient rotary compressor

Terminal block power input

Standard cutout dimension for easy exchange

Every unit functionally tested before shipping

Remote Access Control Units support up to 2 temperature sensors and 10 alarms. They support multiple communication protocols: SNMP, Modbus TCP, Ethernet/IP, and Profinet.

Mounting hardware, gaskets and user manual furnished with the unit

SPECIFIKATIONER

Färg: Ljusgrå
Material: Mjukt stål
Yta: Pulverlackerad
Färgkod: RAL 7035

Table 1/1

Katalognummer	Nominell kapacitet Btu/h	Nominell kapacitet i watt	Nominell spänning	Antal faser	Höjd	Bredd
S101046G031	3400Btu/h	1000W	460V	1	950mm	399mm
S060316G031	1000Btu/h	300W	115V		549mm	279mm
S060326G031	1000Btu/h	300W	230V		549mm	279mm
S060516G031	1700Btu/h	500W	115V		549mm	279mm
S060526G031	1700Btu/h	500W	230V		549mm	279mm
S101016G031	3400Btu/h	1000W	115V		950mm	399mm
S101026G031	3400Btu/h	1000W	230V		950mm	399mm
S101516G031	5000Btu/h	1500W	115V		950mm	399mm
S101526G031	5000Btu/h	1500W	230V		950mm	399mm
S101546G031	5000Btu/h	1500W	460V	3	950mm	399mm
S162026G031	6800Btu/h	2000W	230V		1580mm	399mm
S162046G031	6800Btu/h	2000W	460V	3	1580mm	399mm
S162526G031	8500Btu/h	2500W	230V		1580mm	399mm
S162546G031	8500Btu/h	2500W	460V	3	1580mm	399mm
S164046G031	13500Btu/h	4000W	460V	3	1580mm	500mm
S162016G031	6800Btu/h	2000W	115V		1580mm	399mm

Katalognummer	Nominellkapacitet Btu/h	Nominellkapacitet i watt	Nominell spänning	Antal faser	Höjd	Bredd
S162516G031	8500Btu/h	2500W	115V		1580mm	399mm

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE