

紧凑型 LED 灯 550LM 运动传感器

Data Solutions

物料号

57265



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

认证



功能

Lights can be easily mounted vertically or horizontally.

Simple through-wiring based on a plug-and-play system.

产品属性

交流输入电压: 230V max

附件类型: 灯

直流输入电压: 24V max

防护等级: IP20

长度: 396mm

包装数量: 1

颜色: 黑色

深度: 40mm

完成: 平滑哑光

材料: 塑料

产品类型: 灯

类型: Cabinet Light

宽度: 33mm

色温: 5800K

标称电压: 230V

工作温度: -20 to 55°C

重量: 0.24kg

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE