

IceStop 自调控伴热电缆

Data Solutions



nVent RAYCHEM IceStop self-regulating trace heating cables provide roof and gutter de-icing, suitable for all standard materials of gutters and drainpipes. Power output is 36 W/m at 0 °C in ice water, 18 W/m at 0 °C in air.

功能

设计简单

用于沥青屋顶的 GM-2XT

Easy to install: cut to length, meter marks, simple fast RayClic connections

Safe and efficient in operation: no overheating, even when crossed, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

技术参数

标称厚度:	6mm
标称宽度:	14mm
标称电缆重量:	130g/m
最低安装温度:	-18°C
颜色:	黑色
接地路径类型:	编织网
导体材料:	镀镍铜

Table 1/1					
物料号	订货号	电源电压	在 0°C，230V 时空气环境中的标 称输出功率	在 0°C，230V 时冰水环境中的标 称输出功率	外护套材料
092961-000	GM-2XT	208 – 240V	18W/m	36W/m	含氟聚合物
446105-000	GM-2X	208 – 240V	18W/m	36W/m	改性聚烯烃
832100-000	GM-1X	120V			改性聚烯烃
900069-000	GM-1XT	120V			含氟聚合物

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE