

进线口进线盖板冲头，CEAP

适用于 CCF 和 CEP 进线口系统的 CEAP 冲孔工具。



功能

Delivery: Stamp, die, pull axis, lock nut, plastic case.

Pack quantity: 1 pcs.

Material: 2 mm maximum thickness for S 235 sheet metal.

Description: By using the CEAP sheet metal punching tool, the desired breakout can be made precisely without chips or splintering in only a few minutes. The convenient built-in punch-hole marking tip can be used to punch-mark the drill points clearly for screw-on attachments. These sheet-metal punches are compatible with all common hydraulic pumps.

技术参数

Table 1/1						
物料号	订货号	高度	宽度	深度	产品系列	材料
CEAP14	58379	71mm	71mm	50mm	电缆管理	低碳钢
CEAP01-CEP	58384	61mm	137mm	50mm	电缆管理	低碳钢
CEAP610	58381	71mm	93.5mm	50mm	电缆管理	低碳钢
CEAP816	58382	71mm	116mm	50mm	电缆管理	低碳钢
CEAP1024	58383	71mm	138.5mm	50mm	电缆管理	低碳钢

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE