


RatiopacPRO Style, Front and Rear Trim

Circulating, Screwless Front



RatiopacPRO Style

桌面机箱采用保护框架设计，具有橡胶条，提供多种配置选项。

The Front and Rear Trims with Top & Bottom Rubber Strip option provides connector safeguarding and integrated stacking capability. The Circulated Rubber Strip design protects corner and is ideal for smaller mobile cases. For larger equipment, the Front Handle offers convenient carrying and rear connector protection.

Designed for 19" components with guide rails or proprietary components with a mounting plate, RatiopacPRO Style caters to your specific requirements.

功能

桌面机箱，采用保护框架设计，框架四周均为橡胶条, 提供更多保护

用于 19 寸组件（导轨）或专用组件（安装板）的机箱

建立 EMC 屏蔽, 需要在机箱中添加其他组件

前侧用于无螺钉的前面板安装，后侧用于标准前面板安装

开孔底盖用于空气冷却

无可见螺钉；保护层部件无需工具即可拆卸

适用 160 mm, 220 mm, 280 mm 和 340 mm（取决于机箱深度）

技术参数

产品类型: 仪器箱

类型: 用于安装单个电子器件的仪器箱

产品系列: RatiopacPRO 样式

Table 1/3

物料号	机架高度	机架宽度	深度	包装数量	可用高度	可用宽度
-----	------	------	----	------	------	------

24581-626	6U	42HP	418mm	1	245.7mm	213.9mm
24581-634	6U	63HP	298mm	1	245.7mm	320.6mm
24581-635	6U	63HP	354mm	1	245.7mm	320.6mm
24581-636	6U	63HP	418mm	1	245.7mm	320.6mm
24581-644	6U	84HP	298mm	1	245.7mm	427.3mm
24581-645	6U	84HP	354mm	1	245.7mm	427.3mm
24581-646	6U	84HP	418mm	1	245.7mm	427.3mm
24581-647	6U	84HP	478mm	1	245.7mm	427.3mm
24581-214	2U	28HP	298mm	1	67.9mm	142.8mm
24581-215	2U	28HP	354mm	1	67.9mm	142.8mm
24581-224	2U	42HP	298mm	1	67.9mm	213.9mm
24581-225	2U	42HP	354mm	1	67.9mm	213.9mm
24581-226	2U	42HP	418mm	1	67.9mm	213.9mm
24581-234	2U	63HP	298mm	1	67.9mm	320.6mm
24581-235	2U	63HP	354mm	1	67.9mm	320.6mm
24581-236	2U	63HP	418mm	1	67.9mm	320.6mm
24581-244	2U	84HP	298mm	1	67.9mm	427.3mm

24581-245	2U	84HP	354mm	1	67.9mm	427.3mm
24581-246	2U	84HP	418mm	1	67.9mm	427.3mm
24581-247	2U	84HP	478mm	1	67.9mm	427.3mm
24581-314	3U	28HP	298mm	1	112.3mm	142.8mm
24581-315	3U	28HP	354mm	1	112.3mm	142.8mm
24581-324	3U	42HP	298mm	1	112.3mm	213.9mm
24581-325	3U	42HP	354mm	1	112.3mm	213.9mm
24581-326	3U	42HP	418mm	1	112.3mm	213.9mm
24581-334	3U	63HP	298mm	1	112.3mm	320.6mm
24581-335	3U	63HP	354mm	1	112.3mm	320.6mm
24581-336	3U	63HP	418mm	1	112.3mm	320.6mm
24581-344	3U	84HP	298mm	1	112.3mm	427.3mm
24581-345	3U	84HP	354mm	1	112.3mm	427.3mm
24581-346	3U	84HP	418mm	1	112.3mm	427.3mm
24581-347	3U	84HP	478mm	1	112.3mm	427.3mm
24581-424	4U	42HP	298mm	1	156.8mm	213.9mm
24581-425	4U	42HP	354mm	1	156.8mm	213.9mm

24581-426	4U	42HP	418mm	1	156.8mm	213.9mm
24581-434	4U	63HP	298mm	1	156.8mm	320.6mm
24581-435	4U	63HP	354mm	1	156.8mm	320.6mm
24581-436	4U	63HP	418mm	1	156.8mm	320.6mm
24581-444	4U	84HP	298mm	1	156.8mm	427.3mm
24581-445	4U	84HP	354mm	1	156.8mm	427.3mm
24581-446	4U	84HP	418mm	1	156.8mm	427.3mm
24581-447	4U	84HP	478mm	1	156.8mm	427.3mm
24581-624	6U	42HP	298mm	1	245.7mm	213.9mm
24581-625	6U	42HP	354mm	1	245.7mm	213.9mm

Table 2/3						
物料号	前部框架结构	制冷选项	符合	EMC 屏蔽	完成	高度
24581-626	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	290mm
24581-634	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	290mm

物料号	前部框架结构	制冷选项	符合	EMC 屏蔽	完成	高度
24581-635	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	290mm
24581-636	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	290mm
24581-644	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	290mm
24581-645	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	290mm
24581-646	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	290mm
24581-647	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	290mm

物料号	前部框架结构	制冷选项	符合	EMC 屏蔽	完成	高度
24581-214	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	112mm
24581-215	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	112mm
24581-224	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	112mm
24581-225	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	112mm
24581-226	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	112mm
24581-234	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	112mm

物料号	前部框架结构	制冷选项	符合	EMC 屏蔽	完成	高度
24581-235	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	112mm
24581-236	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	112mm
24581-244	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	112mm
24581-245	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	112mm
24581-246	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	112mm
24581-247	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	112mm

物料号	前部框架结构	制冷选项	符合	EMC 屏蔽	完成	高度
24581-314	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	157mm
24581-315	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	157mm
24581-324	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	157mm
24581-325	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	157mm
24581-326	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	157mm
24581-334	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	157mm

物料号	前部框架结构	制冷选项	符合	EMC 屏蔽	完成	高度
24581-335	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	157mm
24581-336	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	157mm
24581-344	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	157mm
24581-345	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	157mm
24581-346	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	157mm
24581-347	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	157mm

物料号	前部框架结构	制冷选项	符合	EMC 屏蔽	完成	高度
24581-424	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	201mm
24581-425	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	201mm
24581-426	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	201mm
24581-434	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	201mm
24581-435	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	201mm
24581-436	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	201mm

物料号	前部框架结构	制冷选项	符合	EMC 屏蔽	完成	高度
24581-444	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	201mm
24581-445	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	201mm
24581-446	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	201mm
24581-447	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	201mm
24581-624	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	290mm
24581-625	侧面饰件, 水平横梁	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (可改装)	阳极氧化, 钝化, 粉末涂层	290mm

Table 3/3

物料号	材料	防护等级	静态负载	宽度	快速发货
-----	----	------	------	----	------

24581-626	铝	IP30	25kg	247.5mm	No
24581-634	铝	IP30	25kg	354.2mm	No
24581-635	铝	IP30	25kg	354.2mm	No
24581-636	铝	IP30	25kg	354.2mm	No
24581-644	铝	IP30	25kg	460.9mm	No
24581-645	铝	IP30	25kg	460.9mm	No
24581-646	铝	IP30	25kg	460.9mm	No
24581-647	铝	IP30	25kg	460.9mm	No
24581-214	铝	IP30	25kg	176.4mm	No
24581-215	铝	IP30	25kg	176.4mm	No
24581-224	铝	IP30	25kg	247.5mm	No
24581-225	铝	IP30	25kg	247.5mm	No
24581-226	铝	IP30	25kg	247.5mm	No
24581-234	铝	IP30	25kg	354.2mm	No
24581-235	铝	IP30	25kg	354.2mm	No
24581-236	铝	IP30	25kg	354.2mm	No
24581-244	铝	IP30	25kg	460.9mm	No

24581-245	铝	IP30	25kg	460.9mm	No
24581-246	铝	IP30	25kg	460.9mm	No
24581-247	铝	IP30	25kg	460.9mm	No
24581-314	铝	IP30	25kg	176.4mm	No
24581-315	铝	IP30	25kg	176.4mm	No
24581-324	铝	IP30	25kg	247.5mm	No
24581-325	铝	IP30	25kg	247.5mm	No
24581-326	铝	IP30	25kg	247.5mm	No
24581-334	铝	IP30	25kg	354.2mm	No
24581-335	铝	IP30	25kg	354.2mm	No
24581-336	铝	IP30	25kg	354.2mm	No
24581-344	铝	IP30	25kg	460.9mm	No
24581-345	铝	IP30	25kg	460.9mm	No
24581-346	铝	IP30	25kg	460.9mm	No
24581-347	铝	IP30	25kg	460.9mm	No
24581-424	铝	IP30	25kg	247.5mm	No
24581-425	铝	IP30	25kg	247.5mm	No

24581-426	铝	IP30	25kg	247.5mm	No
24581-434	铝	IP30	25kg	354.2mm	No
24581-435	铝	IP30	25kg	354.2mm	No
24581-436	铝	IP30	25kg	354.2mm	No
24581-444	铝	IP30	25kg	460.9mm	No
24581-445	铝	IP30	25kg	460.9mm	No
24581-446	铝	IP30	25kg	460.9mm	No
24581-447	铝	IP30	25kg	460.9mm	No
24581-624	铝	IP30	25kg	247.5mm	No
24581-625	铝	IP30	25kg	247.5mm	No

其他产品详情

有关定制配置（颜色、尺寸等）的信息，请访问我们的在线配置器 (<https://configurators.schroff.biz/ratiopacpro-style>)。

可根据要求提供客户特定版本的改造服务（特殊颜色、尺寸、开孔等）。

没有最小起订量要求。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE