


Operator Interface Control Enclosure, OICE



The mild steel operator interface control enclosure, OICE, has a pre-machined hole pattern to allow for the fixation to a swing arm, plus a removable front plate at an IP 55 protection degree. Components can be easily fitted thanks to the removable front plate, but will also be easily accessible through a rear door. Side handles on the enclosure allow for easy movement of the enclosure into the working position.

工业标准

CE UKCA

EAC

GOST

功能

Material: Body and door are manufactured from 1.2 mm mild steel, front cover and handles manufactured from aluminium.

Body: Folded and seam welded, with maximum opening. The front fitted with an aluminium front panel. Handling grips mounted to front, left and right edges.

Rear door: Surface mounted, with 130° opening. Concealed removable hinges, with captive pin. Hinges can be mounted to allow left or right hand opening. Door profiles MMDP are available as an accessory.

Lock: Customised lock, with double grip for easy opening of the door. Double-bit 3 mm insert and 90° movement. Other inserts and locks are available as an accessory.

Protection: IP 55, IK 10.

Finish: RAL 7035 structured powder coating. Top bottom profile RAL7016.

Delivery: Enclosure with aluminium front panel, rear door, plastic double-bit 3 mm key and mounting accessories.

技术参数

材料:	铝; 铝
颜色:	浅灰色
完成:	粉末涂层
颜色代码:	RAL 7035

Table 1/1					
物料号	高度	宽度	深度	重量	快速发货
OICE303015	300mm	300mm	155mm	4.5kg	No
OICE304021	300mm	400mm	210mm	6.3kg	No
OICE404021	400mm	400mm	210mm	7.3kg	No
OICE406021	400mm	600mm	210mm	9.7kg	No
OICE505021	500mm	500mm	210mm	10.1kg	No
OICE506021	500mm	600mm	210mm	11.3kg	No
OICE606021	600mm	600mm	210mm	11.3kg	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE