

RayClic 连接套件

Data Solutions



nVent RAYCHEM RayClic connection system is a simple, fast and reliable set of connection kits developed for select nVent RAYCHEM XL-Trace, IceStop and HWAT self-regulating heating cables. No heat guns or wire stripping are needed, because insulation displacement technology is used to make the electrical connection.

功能

冷施工，无需热风枪，无需特殊工具

Simple, fast, intuitive connection: no wire stripping or special tools needed

Lower total installed system cost, due to reduced installation time: cold applied, no heat guns or special tools needed

Reliable during long life: 10 year extended product warranty available, maintenance free

技术参数

最大暴露温度: 65°C

连接类型: 冷敷

颜色: 灰色

Table 1/1

物料号	订货号	型号	额定电压	额定电流
441524-000	RAYCLIC-T-02	T 分支	240V	20A
001013-000	RAYCLIC-X-02	X 分支	240V	20A

物料号	订货号	型号	额定电压	额定电流
364855-000	RAYCLIC-S-02	加热电缆/加热电缆	240V	20A
716976-000	RAYCLIC-PS-02	两根发热电缆的电源连接	240V	20A
235422-000	RAYCLIC-CE-02	一根发热电缆的电源连接	240V	20A
636284-000	RAYCLIC-PT-02	电源连接和 T 形分支	240V	20A
559871-000	RAYCLIC-S-03	加热电缆/加热电缆	120 – 277V	30A
014023-000	RAYCLIC-T-03	T 分支	120 – 277V	30A
233053-000	RAYCLIC-PC-03	一根发热电缆的电源连接	120 – 277V	30A

其他产品详情

要正确设计和安装 RayClic 连接系统，请使用连接套件随附的相应产品设计指南和安装说明。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE