


Thermostat, ETR



This adjustable temperature thermostat, ETR, for any enclosure, with either a normally open (NO) or normally closed (NC) contact, is used to control installed devices. Such devices could be a filter fan or a fan heater, that should turn on or off at the required temperature level, set by the user. The result is reduced operational cost.

工业标准

符合 UL 508A 认证 元件

cULus_UL Listed

CE

UKCA

EAC

功能

Description: Thermostat with NC/NO contacts to manage temperature in panels. ETR202 with a normally closed contact for regulating heaters. ETR201 with a normally open contact for regulating cooling devices or signal devices. Sensor element thermostatic bimetal. Mounting clip for 35 mm DIN rail (EN 60715).

Material: Plastic according to UL94 V-0.

Setting range: 0 °C to +60 °C. Switching temperature difference less than 7 °K, and switching point tolerance ± 4 °K.

Switch capacity: 240 V AC, 10(2) A. 120 V AC, 15(2) A. 24 V DC, 30 W. Value in brackets for inductive load.

Operating temperature: -20 °C to +80 °C.

Service life: > 100,000 cycles.

Connection: Screw terminal for cable (0.5 to 2.5 mm²).

Protection: IP 20.

Approvals: CE, EAC, cULus_UL Listed.

Finish: RAL 7035.

Pack quantity: 1 piece.

Switch capacity: 240 V AC, 10(2) A. 120 V AC, 15(2) A. 24 V DC, 30 W; value in brackets for inductive load

Operating temperature: -20 °C to +80 °C

Service life: > 100,000 cycles

Connection: Screw terminal for cable (0.5 to 2.5 mm²)

技术参数

Table 1/1						
物料号	高度	宽度	深度	材料	完成	颜色
ETR202	72mm	40mm	43mm	塑料	平滑	浅灰色
ETR201	72mm	40mm	36mm	塑料	平滑	浅灰色

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE