

# Thermostat, ETR200



This adjustable temperature thermostat, ETR200, for any enclosure, with either a normally open (NO) and normally closed (NC) contact, is used to control installed devices. Such devices could be a filter fan or a fan heater, that should turn on or off at the required temperature level, set by the user. The result is reduced operational cost. The product's versatility is high, since either cooling or heating can be controlled by the two different types of contacts that are housed within the same thermostat.

## 工业标准

符合 UL 508A 认证 元件

cULus\_UL Listed

CE

EAC

## 功能

Description: Thermostat with changeover contact to manage any kind of device, heater or cooling. Sensor element thermostatic bimetal. Mounting clip for 35 mm DIN rail (EN 60715).

Material: Plastic according to UL94 V-0.

Setting range: 0 °C to +60 °C. Switching temperature difference less than 3 °K, and switching point tolerance  $\pm 3$  °K.

Switch capacity: NC contact, 100-250 V AC, 10(2) A. NO contact, 100-250 V AC, 5(2) A, for 230 V AC operation only. 24 V DC, 30 W. Value in brackets for inductive load.

Operating temperature: -40 °C to +80 °C.

Service life: > 100,000 cycles.

Connection: Screw terminal for cable (0.5 to 2.5 mm<sup>2</sup>).

Protection: IP 20.

Approvals: CE, EAC, cULus\_UL Listed.

Finish: RAL 7035.

Pack quantity: 1 piece.

Setting range: 0 °C to +60 °C; switching temperature difference less than 3 °K, and switching point tolerance  $\pm 3$  °K

Switch capacity: NC contact, 100-250 V AC, 10(2) A. NO contact, 100-250 V AC, 5(2) A, for 230 V AC operation only; 24 V DC, 30 W; value in brackets for inductive load

Operating temperature: -40 °C to +80 °C

Service life: > 100,000 cycles

技术参数

Table 1/1						
物料号	高度	宽度	深度	材料	完成	颜色
ETR200	60mm	37mm	53mm	塑料	平滑	浅灰色

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE