

Thermostat Kit, BPT



The thermostat limits the flow of compressed air, in order for it to be used in situations when cooling is really needed. This saves compressed air, which reduces the operating costs.

功能

Description: Brass solenoid valve and thermostat that limit the flow of compressed air to only when cooling is needed. The thermostat is factory set at 35 °C, but adjustable to any other temperature. The thermostat mounts in a 22 mm diameter hole, and it may be mounted through the enclosure wall or on a bracket inside the enclosure. The thermostatically controlled vortex cooler saves compressed air, and it is recommended where heat load fluctuates and continual purge is not required.

Voltage: 240 V and 50 Hz. Other voltages on request.

Delivery: Thermostat with mounting bracket, and solenoid valve.

This is particular important when mounting a vortex cooler due to the high operating costs to compress air

Brass solenoid valve and thermostat that limit the flow of compressed air to only when cooling is needed

The thermostat is factory set at 35 °C, but adjustable to any other temperature

The thermostat mounts in a 22 mm diameter hole, and it may be mounted through the enclosure wall or on a bracket inside the enclosure

The thermostatically controlled vortex cooler saves compressed air, and it is recommended where heat load fluctuates and continual purge is not required

Voltage: 240 V and 50 Hz. Other voltages on request

Delivery: Thermostat with mounting bracket, and solenoid valve

技术参数

Table 1/1					
物料号	外壳材料	产品系列	材料	完成	快速发货
BPT14	黄铜	气候控制	黄铜	研磨	No
BPT38	黄铜	气候控制	黄铜	研磨	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE