


Universal Busbar Adapter 200-250A, WO60



Universal busbar adapters with movable fastening rails.

工业标准

UL
CSA
GL
DNV-GL

功能

Description: 3-pole universal busbar adapter 200 - 250 A, with movable fastening rails with M4 slide nuts for safe mounting of the switching devices.

Rated voltage: 690 V

For busbars: 12, 15, 20, 25, 30 × 5, 10

Power dissipation at 80% load: 10.6 W (32214), 22.2 W (32168)

Pack quantity: 1 pc.

Approvals: CSA,UL,GL DNV GL

For busbars: 12, 15, 20, 25, 30 × 5, 10

Power dissipation at 80% load: 10.6 W (32214), 22.2 W (32168)

技术参数

Table 1/1						
物料号	高度	宽度	深度	材料	完成	颜色
32168	320mm	110mm	101mm	塑料, 钢	平滑	浅灰色
32214	222mm	108mm	101mm	塑料, 钢	平滑	浅灰色

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE