

Elexant 650c-Modbus Control Unit



The nVent RAYCHEM Elexant 650c-Modbus controller is designed for operation with the nVent RAYCHEM heating cables for roof and gutter de-icing and surface snow melting applications.

功能

Intuitive set-up and programming of the unit with a 4,3" colour touch screen

Flexible temperature control of roof & gutter de-icing and surface snow melting systems

Controls 2 independent heating circuits

带转换触点的警报继电器，用于解决信号功率、温度或通信问题

Ambient temperature monitoring with high and low temperature alarm

Offsite configurable - can be set up prior to final installation

DIN rail panel mountable

The Elexant 650c-Modbus is equipped with a RS485 port for Modbus communication to a BMS system which can be used for configuration, monitoring and alarm purposes

Ice rain feature - preheating the surface to prevent the issue of freezing rain (for surface snow melting application only)

技术参数

Table 1/3

物料号	警报继电器	通信	通信协议	深度	危险区域	高度
1244-022835	是	是	Modbus RTU	155 mm	否	110 mm

Table 2/3

物料号	IP 等级	安装	输出继电器	传感器类型	电源电压	温度控制范围
-----	-------	----	-------	-------	------	--------

1244-022835	IP20	DIN 导轨	2 x 4 A @ 230 VAC	NTC	230 – 253 V	–20 to 30 °C
-------------	------	--------	----------------------	-----	-------------	--------------

Table 3/3

物料号	宽度
1244-022835	55 mm

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

亚太地区

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

拉丁美洲

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT