


EuropacPRO 19" Subrack Kit for Backplane, Heavy, Shielded, Front Handle

电力公用事业

用于安装背板的 EMC 屏蔽型插箱，重型版本带有 tox 连接侧板和前把手。



认证



功能

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded) and includes handles

提供改制，如开孔、各种表面或尺寸

扁平包装，节省空间

铝结构

“重”型水平横梁

用于安装背板的后水平横梁，带绝缘条

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

内部和外部尺寸符合：IEC 60297-3-100, -101, IEEE 1101.1

IP 20, in accordance with IEC 60529

技术参数

Table 1/3

物料号	机架高度	深度	包装数量	用于安装	板深度	EMC 垫片类型
24567-172	3 U	235 mm	1	背板	160 mm, 220 mm	泡棉
24567-173	3 U	295 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉
24567-174	3 U	355 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉
24567-472	6 U	235 mm	1	背板	160 mm, 220 mm	泡棉
24567-473	6 U	295 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉
24567-474	6 U	355 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉

Table 2/3

物料号	耐冲击和振动性	包含把手	安装	符合	EMC 屏蔽	产品类型
24567-172	5 g (force)	是	机架	IEC 60297-3-103	是	插箱/机箱
24567-173	5 g (force)	是	机架	IEC 60297-3-103	是	插箱/机箱
24567-174	5 g (force)	是	机架	IEC 60297-3-103	是	插箱/机箱
24567-472	5 g (force)	是	机架	IEC 60297-3-103	是	插箱/机箱
24567-473	5 g (force)	是	机架	IEC 60297-3-103	是	插箱/机箱
24567-474	5 g (force)	是	机架	IEC 60297-3-103	是	插箱/机箱

Table 3/3

物料号	机架宽度	静态负载
24567-172	84 HP	15 kgf
24567-173	84 HP	15 kgf
24567-174	84 HP	15 kgf
24567-472	84 HP	15 kgf
24567-473	84 HP	15 kgf
24567-474	84 HP	15 kgf

ADDITIONAL PRODUCT DETAILS

单个配置：支持大范围高度、宽度和深度；根据不同应用可选多种规格导轨；内部选项；附件和安装材料。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE