

Raystat EX-02 Mechanical Thermostat



nVent RAYCHEM Raystat-EX-02 is a hazardous area mechanical surface sensing thermostat providing temperature control for heating cables. Switching temperature range -4°C to 163°C , adjustable externally to the Ex enclosure by a dial mounted under a bolted-on cover and seal. Switching current capacity is 22 A.

功能

Simple to install and operate: supplied with 3 m long stainless steel fluid filled bulb and capillary, single cable entry through 3/4" NPT thread with nVent RAYCHEM cable glands available to suit non-armoured/armoured cables

Energy saving, line-sensing electronic control thermostat

Adjustable set point: -4°C to 163°C (externally to the Ex enclosure by dial mounted under bolted-on cover and seal)

Direct switching, maximum current 16 A, 230 VAC: single pole change-over with volt-free contacts, SPDT

Lightweight cast aluminium with stainless steel fittings, can be pipe mounted using nVent RAYCHEM support brackets or surface mounted

技术参数

额定电流:	22 A
深度:	101.5 mm
宽度:	114.5 mm
高度:	167 mm
控制器温度设置:	-4 to 163°C
材料:	铝
恒温器类型:	机械恒温器

物料号	项目名称
J0000261	RAYSTAT-EX-02-J

物料号	项目名称
404385-000	RAYSTAT-EX-02

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com	Europe, Middle East, Africa Tel +32.16.213.511 Fax +32.16.213.604 thermal.info@nvent.com	Asia Pacific Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com	Latin America Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com
--	--	---	--