

适用于 VMEbus 的电源，19" 交流/直流

适用 VMEbus 应用的可插拔 19" 电源。



认证



功能

宽幅输入电压：90 ... 264 VAC 和 130 ... 350 VDC，带主动功率因数校正 (PFC) 功能

VMEBus 信号

3 种输出电压

技术参数

Table 1/3

物料号	类型	搭配	交流输入电压	电源	输出电压数	电压 1
13100-205	19" 开关模式	VMEbus 系统	90 – 264V	150W	3	5V
13100-203	19" 开关模式	VMEbus 系统	90 – 264V	224W	3	5V
13100-204	19" 开关模式	VMEbus 系统	90 – 264V	224W	3	5V

Table 2/3						
物料号	电流 1	电压 2	电流 2	电压 3	电流 3	机架高度
13100-205	20A	12V	4A	-12V	3A	6U
13100-203	28A	12V	7A	-12V	3A	6U
13100-204	28A	15V	5.6A	-15V	2.4A	6U

Table 3/3				
物料号	机架宽度	深度	包装数量	快速发货
13100-205	8HP	171.93mm	1	No
13100-203	12HP	171.93mm	1	No
13100-204	12HP	171.93mm	1	No

其他产品详情

输出数据在 TU = 0 ... 40 °C 环境下测得。

输出功率 V2 + V3 = 60 W。

Output currents (UL values in bracket): V1 = 5 V / I1 = 20 A (18 A)V2 = 12 V / I2 = 4 A (3 A)V3 = - 12 V / I3 = 3 A (2 A).

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE