


VME64x 系统，1 U，2 个插槽，ATX PSU

物料号

20836-145



VME64x 系统，适用于 2 个水平安装的 VME64x 板，6 U，160 mm。可选后部 I/O。通过 Open Frame 电源为系统供电。带 4 个风扇的热插拔风扇盘可提供出色的冷却效果。

认证



功能

系统符合 IEC 60297 - 3 - 101, 102, 103 标准以及 IEEE 1101.1, 1101.10/11 标准；背板符合 VITA 1.1 - 1997 标准

Backplane VME64x, 2 槽, 6 U, 带 P0 连接器

散热方式：风扇托盘，内含 4 个风扇，风道：从右至左侧；支持风扇转速监测和电压显示

电路板水平安装，电路板规格；前部：6 U, 160 mm 深；, 后部 I/O：6 U, 80 mm 深

ATX PSU, 250 W

产品属性

产品类型: 系统

插槽数: 2

类型: 19" 机架安装

背板类型: 6 U VME64 扩展

数据传输: VME64; VME2eSST

每插槽的功率: 30W

交流输入电压: 100 – 240V

气流方向: 从右到左

机架高度: 1U

电源类型: 1块 ATX PSU

包含电源: 是

后部 I/O: 是

符合: ANSI/VITA 1.1-1997

深度: 277.5mm

高度: 44.64mm

宽度: 449mm

电源: 200W

包装数量: 1

其他产品详情

可应要求提供定制系统。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE