

Vertical Mount Outdoor Air Conditioner, E-NOX



This outdoor vertical cooling unit, E-NOX, with a IP55 - NEMA TYPE 4 (4X Stainless Steel frame) protection degree, is available in many different sizes for different outdoor cooling requirements. This means that the right cooling solution can be chosen easily. The cooling unit is easy to install and is also available in stainless steel for harsh environments.

认证



功能

Advanced Microport : Allows users to configure whether the internal fan should remain active or be disabled when the microport is opened.

ECO Mode: Integrated as standard across the entire range to optimize energy efficiency and reduce power consumption.

Temperature Unit Conversion (°C / °F) : Seamlessly switch between Celsius and Fahrenheit by modifying a single parameter.

Predictive Maintenance : A smart self-learning system monitors performance and notifies users when maintenance is required, minimizing downtime.

Service Mode : Enables a quick diagnostic check to verify correct operation of the unit.

Water Condense management : All models are equipped with an external condensate discharge system, from 1000 W and above. This energy-free system eliminates condensate without requiring external drainage or power supply.

Integrated Strip Seals : Factory-installed sealing strips ensure a perfect fit between the air conditioner and the electrical enclosure, providing high IP protection and simplifying installation.

Magnetic Filter Mounting System : Simplifies filter replacement while preserving the sleek, modern design of the E-NEXT range.

Digital Thermostat (TX-i40) : Offers full control and flexibility with an intuitive interface and advanced connectivity options, in NOX series thermostat is provided with 3 meter cable with a din bar metal support to be fixed into the enclosure, so display will be protected against water and dust.

Condenser surface coating : surface coating will prevent condenser failure due harsh environment.

技术参数

Table 1/4

物料号	制冷能力, L35 L35	制冷能力, L35 L50	标称电压	相数	频率	材料
NOX16B0E1U0 0000	1600W	1100W	230V	1Ph	50/60 HzHz	镀锌钢
NOX40B0E1U0 0000	3850W	2650W	230V	1Ph	50/60 HzHz	镀锌钢
NOX20B0E1U0 0000	2000W	1500W	230V	1Ph	50/60 HzHz	镀锌钢

Table 2/4

物料号	颜色代码	高度	工作温度	环境温度	宽度	深度
NOX16B0E1U0 0000	RAL 7035	1000mm	-20 to 55°C	20 – 45°C	400mm	250mm
NOX40B0E1U0 0000	RAL 7035	1270mm	-20 to 55°C	20 – 45°C	500mm	336mm
NOX20B0E1U0 0000	RAL 7035	1000mm	-20 to 55°C	20 – 45°C	400mm	250mm

Table 3/4

物料号	最大电流	T 保险丝	噪音等级	浪涌电流	机柜风扇容量	功耗, L35L35
NOX16B0E1U0 0000	4.3A	8A	65dB(A)	19.7A	540m³/h	720W

物料号	最大电流	T 保险丝	噪音等级	浪涌电流	机柜风扇容量	功耗, L35L35
NOX40B0E1U0000	7.8A	16A	70dB(A)	37A	1500m³/h	1670W
NOX20B0E1U0000	4.8A	10A	77dB(A)	21.8A	540m³/h	990W

Table 4/4		
物料号	功耗, L35L50	快速发货
NOX16B0E1U00000	820W	No
NOX40B0E1U00000	1980W	No
NOX20B0E1U00000	1130W	No

其他产品详情

Integrated Modbus RTU (RS485) Available for all units equipped with the TX-i40 thermostat, enabling seamless integration into industrial communication networks.

Advanced Sequencing Allows two units to operate in coordinated sequence for load balancing and redundancy, extending system lifespan.

Low-Noise Version Optional configuration with modulated-speed fans for quiet operation in residential or noise-sensitive commercial environments.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE