


VMEBus 系统，7 U，12 槽，Open Frame PSU

物料号

20836-715



VME 系统，适用 12 个 VME 板卡，6 U，160 mm。通过 Open Frame 电源为系统供电。风扇控制模块用于监测风扇、温度和电压。

认证



功能

系统符合 IEC 60297 - 3 - 101、- 102、- 103 标准以及 IEEE 1101.1、, 1101.10/11 标准；背板符合 VITA 1.1 - 1994 标准

PSU, 开放式, 444 W (电压低于 180 VAC 时, 400 W)

12 槽 VME 背板, 6 U, 符合 VITA 1-1994 标准的 J1/J2 整体式背板

通过 1 个风扇散热 (风扇托盘), 从下到上冷却; 通过风扇控制模块 (FCM) 控制温度

带直流工作电压显示模块, 支持风扇和温度告警

产品属性

产品类型: 系统

插槽数: 12

类型: 19" 机架安装

背板类型: 6 U VME64

数据传输: VME64; VME2eSST

每插槽的功率: 30W

交流输入电压: 100 – 240V

气流方向: 从下至上

机架高度: 7U

电源类型: 开放式框架

包含电源: 是

后部 I/O: 否

符合: ANSI/VITA 1.1 - 1994

深度: 355mm

高度: 310.35mm

宽度: 449mm

电源: 450W

包装数量: 1

其他产品详情

可应要求提供定制系统。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE