

[illegible]

认证



功能

适用 EMC 织物垫片

技术参数

深度 (D):	2.5mm
材料:	铝
完成:	阳极氧化; 钝化
附件类型:	前面板
产品类型:	前面板
类型:	不带把手的前面板
EMC 屏蔽:	无 (可改装)

Table 1/3

物料号	机架高度	机架宽度	包装数量	安装	EMC 垫片类型	正面表面处理
20848-260	2U	42HP	1	正面螺钉安装	织物	阳极氧化
20848-261	2U	63HP	1	正面螺钉安装	织物	阳极氧化
20848-027	3U	28HP	1	正面螺钉安装	织物	阳极氧化
20848-047	3U	42HP	1	正面螺钉安装	织物	阳极氧化
20848-068	3U	63HP	1	正面螺钉安装	织物	阳极氧化
20848-097	3U	84HP	1	正面螺钉安装	织物	阳极氧化
20848-269	4U	42HP	1	正面螺钉安装	织物	阳极氧化
20848-270	4U	42HP	1	正面螺钉安装	织物	阳极氧化
20848-271	4U	84HP	1	正面螺钉安装	织物	阳极氧化
20848-189	6U	84HP	1	正面螺钉安装	织物	阳极氧化
20848-013	3U	14HP	1	正面螺钉安装	织物	阳极氧化
20848-015	3U	16HP	1	正面螺钉安装	织物	阳极氧化
20848-020	3U	21HP	1	正面螺钉安装	织物	阳极氧化
20848-106	6U	14HP	1	正面螺钉安装	织物	阳极氧化
20848-108	6U	16HP	1	正面螺钉安装	织物	阳极氧化
20848-113	6U	21HP	1	正面螺钉安装	织物	阳极氧化

物料号	机架高度	机架宽度	包装数量	安装	EMC 垫片类型	正面表面处理
20848-120	6U	28HP	1	正面螺钉安装	织物	阳极氧化
20848-139	6U	42HP	1	正面螺钉安装	织物	阳极氧化
20848-160	6U	63HP	1	正面螺钉安装	织物	阳极氧化
20848-206	2U	28HP	1	正面螺钉安装	织物	阳极氧化
20848-262	2U	84HP	1	正面螺钉安装	织物	阳极氧化
20848-268	4U	28HP	1	正面螺钉安装	织物	阳极氧化
20848-280	9U	84HP	1	正面螺钉安装	织物	阳极氧化
20848-647	5U	28HP	1	正面螺钉安装	织物	阳极氧化
20848-648	5U	42HP	1	正面螺钉安装	织物	阳极氧化
20848-649	5U	63HP	1	正面螺钉安装	织物	阳极氧化
20848-650	5U	84HP	1	正面螺钉安装	织物	阳极氧化
30848-354	3U	4HP	1	正面螺钉安装	织物	阳极氧化
30848-355	6U	4HP	1	正面螺钉安装	织物	阳极氧化
30848-356	3U	8HP	1	正面螺钉安装	织物	阳极氧化
30848-357	6U	8HP	1	正面螺钉安装	织物	阳极氧化
30848-358	3U	12HP	1	正面螺钉安装	织物	阳极氧化
30848-359	6U	12HP	1	正面螺钉安装	织物	阳极氧化

物料号	机架高度	机架宽度	包装数量	安装	EMC 垫片类型	正面表面处理
30848-378	3U	5HP	1	正面螺钉安装	织物	阳极氧化
30848-379	6U	5HP	1	正面螺钉安装	织物	阳极氧化
30848-380	3U	6HP	1	正面螺钉安装	织物	阳极氧化
30848-381	6U	6HP	1	正面螺钉安装	织物	阳极氧化
30848-382	3U	7HP	1	正面螺钉安装	织物	阳极氧化
30848-383	6U	7HP	1	正面螺钉安装	织物	阳极氧化
30848-384	3U	9HP	1	正面螺钉安装	织物	阳极氧化
30848-385	3U	9HP	1	正面螺钉安装	织物	阳极氧化
30848-386	3U	10HP	1	正面螺钉安装	织物	阳极氧化
30848-387	6U	10HP	1	正面螺钉安装	织物	阳极氧化
30849-001	3U	2HP	1	正面螺钉安装	织物	阳极氧化
30849-002	6U	2HP	1	正面螺钉安装	织物	阳极氧化
30849-004	3U	3HP	1	正面螺钉安装	织物	阳极氧化
30849-005	6U	3HP	1	正面螺钉安装	织物	阳极氧化

Table 2/3						
物料号	反面表面处理	边缘处理	符合	高度 (H)	宽度 (W)	认证
20848-260	导电	否	IEC 60297-3-101, IEEE 1101.1/10	84mm	213mm	

物料号	反面表面处理	边缘处理	符合	高度 (H)	宽度 (W)	认证
20848-261	导电	否	IEC 60297-3-101, IEEE 1101.1/10	84mm	319.7mm	
20848-027	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	141.9mm	RoHS
20848-047	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	213mm	RoHS
20848-068	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	319.7mm	RoHS
20848-097	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	426.4mm	RoHS
20848-269	导电	否	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	213mm	RoHS
20848-270	导电	否	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	213mm	RoHS
20848-271	导电	否	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	426.4mm	RoHS
20848-189	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	426.4mm	RoHS
20848-013	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	70.8mm	RoHS
20848-015	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	80.9mm	RoHS
20848-020	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	106.3mm	RoHS

物料号	反面表面处理	边缘处理	符合	高度 (H)	宽度 (W)	认证
20848-106	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	70.8mm	RoHS
20848-108	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	80.9mm	RoHS
20848-113	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	106.3mm	RoHS
20848-120	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	141.9mm	RoHS
20848-139	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	213mm	RoHS
20848-160	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	319.7mm	RoHS
20848-206	导电	否	IEC 60297-3-101, IEEE 1101.1/10	84mm	141.9mm	
20848-262	导电	否	IEC 60297-3-101, IEEE 1101.1/10	84mm	426.4mm	RoHS
20848-268	导电	否	IEC 60297-3-101, IEEE 1101.1/10	172.9mm	141.9mm	RoHS
20848-280	导电	否	IEC 60297-3-101, IEEE 1101.1/10	395.1mm	426.4mm	RoHS
20848-647	导电	否	IEC 60297-3-101, IEEE 1101.1/10	217.4mm	141.9mm	
20848-648	导电	否	IEC 60297-3-101, IEEE 1101.1/10	217.4mm	213mm	

物料号	反面表面处理	边缘处理	符合	高度 (H)	宽度 (W)	认证
20848-649	导电	否	IEC 60297-3-101, IEEE 1101.1/10	217.4mm	319.7mm	
20848-650	导电	否	IEC 60297-3-101, IEEE 1101.1/10	217.4mm	426.4mm	
30848-354	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	20mm	RoHS
30848-355	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	20mm	RoHS
30848-356	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	40.3mm	RoHS
30848-357	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	40.3mm	RoHS
30848-358	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	60.6mm	RoHS
30848-359	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	60.6mm	RoHS
30848-378	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	25mm	RoHS
30848-379	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	25mm	RoHS
30848-380	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	30.1mm	RoHS
30848-381	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	30.1mm	RoHS

物料号	反面表面处理	边缘处理	符合	高度 (H)	宽度 (W)	认证
30848-382	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	35.2mm	RoHS
30848-383	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	35.2mm	RoHS
30848-384	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	45.38mm	
30848-385	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	45.38mm	
30848-386	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	50.5mm	RoHS
30848-387	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	50.5mm	RoHS
30849-001	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	9.8mm	RoHS
30849-002	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	9.8mm	RoHS
30849-004	导电	否	IEC 60297-3-101, IEEE 1101.1/10	128.4mm	14.9mm	RoHS
30849-005	导电	否	IEC 60297-3-101, IEEE 1101.1/10	261.8mm	14.9mm	

Table 3/3	
物料号	快速发货
20848-260	No
20848-261	No

物料号	快速发货
20848-027	No
20848-047	No
20848-068	No
20848-097	No
20848-269	No
20848-270	No
20848-271	No
20848-189	No
20848-013	No
20848-015	No
20848-020	No
20848-106	No
20848-108	No
20848-113	No
20848-120	No
20848-139	No
20848-160	No

物料号	快速发货
20848-206	No
20848-262	No
20848-268	No
20848-280	No
20848-647	No
20848-648	No
20848-649	No
20848-650	No
30848-354	No
30848-355	No
30848-356	No
30848-357	No
30848-358	No
30848-359	No
30848-378	No
30848-379	No
30848-380	No

物料号	快速发货
30848-381	No
30848-382	No
30848-383	No
30848-384	No
30848-385	No
30848-386	No
30848-387	No
30849-001	No
30849-002	No
30849-004	No
30849-005	No

其他产品详情

请单独订购紧固零件（螺钉套，凸缘螺钉）。


2 ... 12 HP 和 14 ... 84 HP 之间外观面差异。

2 ...12 HP：单部件U型

请单独订购 EMC 泡棉垫片。

Standard pack quantity: 2 to 28HP: 5 件, 42 to 84 HP: 1 件, supplied in standard pack quantities (SPQ) only.

14 ... 84 HP: multi-part U-profile (front panel with crimped profiles).



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE