

Front Panel, Front Anodized, Rear Conductive, Unshielded

Servizi di distribuzione di energia

Front panel, unshielded, front anodized and rear conductive.



CERTIFICAZIONI



CARATTERISTICHE

Partial width front panel, Al, 2.5 mm

AI, front anodized, conductive

SPECIFICHE

| Table 1/3 | | | | | | | |
|--------------------|-------------|------------|---------------------|-------------|----------------|--------------|--|
| Numero catalogo | Rack Height | Rack Width | Package Quantity | Handle Type | Montaggio | Front Finish | |
| 30838-123 | 3 U | 84 HP | 1 | Nessuno | Screw-on Front | Anodized | |
| 30838-204 | 6 U | 84 HP | 1 | Nessuno | Screw-on Front | Anodized | |

| Numero catalogo | Rack Height | Rack Width | Package Quantity | Handle Type | Montaggio | Front Finish |
|--------------------|-------------|------------|---------------------|-------------|----------------|--------------|
| 30847-465 | 4 U | 84 HP | 1 | Nessuno | Screw-on Front | Anodized |
| 30847-469 | 5 U | 84 HP | 1 | Nessuno | Screw-on Front | Anodized |
| 30847-461 | 2 U | 84 HP | 1 | Nessuno | Screw-on Front | Anodized |
| 30838-081 | 3 U | 42 HP | 1 | Nessuno | Screw-on Front | Anodized |
| 30838-102 | 3 U | 63 HP | 1 | Nessuno | Screw-on Front | Anodized |
| 30838-162 | 6 U | 42 HP | 1 | Nessuno | Screw-on Front | Anodized |
| 30838-183 | 6 U | 63 HP | 1 | Nessuno | Screw-on Front | Anodized |
| 30847-459 | 2 U | 42 HP | 1 | Nessuno | Screw-on Front | Anodized |
| 30847-460 | 2 U | 63 HP | 1 | Nessuno | Screw-on Front | Anodized |
| 30847-463 | 4 U | 42 HP | 1 | Nessuno | Screw-on Front | Anodized |
| 30847-464 | 4 U | 63 HP | 1 | Nessuno | Screw-on Front | Anodized |
| 30847-467 | 5 U | 42 HP | 1 | Nessuno | Screw-on Front | Anodized |
| 30847-468 | 5 U | 63 HP | 1 | Nessuno | Screw-on Front | Anodized |
| 30847-458 | 2 U | 28 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30847-470 | 3 U | 2 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-067 | 3 U | 28 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-043 | 3 U | 4 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-044 | 3 U | 5 HP | 5 | Nessuno | Screw-on Front | Anodized |

| Numero catalogo | Rack Height | Rack Width | Package Quantity | Handle Type | Montaggio | Front Finish |
|--------------------|-------------|------------|---------------------|-------------|----------------|--------------|
| 30838-045 | 3 U | 6 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-046 | 3 U | 7 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-047 | 3 U | 8 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-049 | 3 U | 10 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-051 | 3 U | 12 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-053 | 3 U | 14 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-055 | 3 U | 16 HP | | Nessuno | Screw-on Front | Anodized |
| 30838-060 | 3 U | 21 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30847-471 | 3 U | 3 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30847-476 | 4 U | 4 HP | 5 | | Screw-on Front | Anodized |
| 30847-462 | 4 U | 28 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-124 | 6 U | 4 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30847-466 | 5 U | 28 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-125 | 6 U | 5 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-126 | 6 U | 6 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-127 | 6 U | 7 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-128 | 6 U | 8 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-130 | 6 U | 10 HP | 5 | Nessuno | Screw-on Front | Anodized |

| Numero catalogo | Rack Height | Rack Width | Package Quantity | Handle Type | Montaggio | Front Finish |
|--------------------|-------------|------------|---------------------|-------------|----------------|--------------|
| 30838-132 | 6 U | 12 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-134 | 6 U | 14 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-136 | 6 U | 16 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-141 | 6 U | 21 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30838-148 | 6 U | 28 HP | 5 | Nessuno | Screw-on Front | Anodized |
| 30847-480 | 9 U | 8 HP | 5 | | Screw-on Front | Anodized |
| 30847-482 | 9 U | 10 HP | 5 | | Screw-on Front | Anodized |
| 30847-484 | 9 U | 12 HP | 5 | | Screw-on Front | Anodized |
| 30847-556 | 9 U | 84 HP | 5 | Nessuno | Screw-on Front | Anodized |

| | | | Table 2/3 | | | |
|-----------------|-------------|---------------|--|---------------|----------|-----------|
| Numero catalogo | Rear Finish | Treated Edges | È conforme a | EMC Shielding | Altezza | Materiale |
| 30838-123 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30838-204 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |
| 30847-465 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 172.9 mm | Alluminio |
| 30847-469 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 217.4 mm | Alluminio |
| 30847-461 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 84 mm | Alluminio |
| 30838-081 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |

| Numero catalogo | Rear Finish | Treated Edges | È conforme a | EMC Shielding | Altezza | Materiale |
|--------------------|-------------|---------------|--|---------------|----------|-----------|
| 30838-102 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30838-162 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |
| 30838-183 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |
| 30847-459 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 84 mm | Alluminio |
| 30847-460 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 84 mm | Alluminio |
| 30847-463 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 172.9 mm | Alluminio |
| 30847-464 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 172.9 mm | Alluminio |
| 30847-467 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 217.4 mm | Alluminio |
| 30847-468 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 217.4 mm | Alluminio |
| 30847-458 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 84 mm | Alluminio |
| 30847-470 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30838-067 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30838-043 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30838-044 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |

| Numero catalogo | Rear Finish | Treated Edges | È conforme a | EMC Shielding | Altezza | Materiale |
|--------------------|-------------|---------------|--|---------------|----------|-----------|
| 30838-045 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30838-046 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30838-047 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30838-049 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30838-051 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30838-053 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30838-055 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30838-060 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30847-471 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 128.4 mm | Alluminio |
| 30847-476 | Conductive | No | | No | 395.1 mm | Alluminio |
| 30847-462 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 172.9 mm | Alluminio |
| 30838-124 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |
| 30847-466 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 217.4 mm | Alluminio |
| 30838-125 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |

| Numero catalogo | Rear Finish | Treated Edges | È conforme a | EMC Shielding | Altezza | Materiale |
|-----------------|-------------|---------------|--|---------------|----------|-----------|
| 30838-126 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |
| 30838-127 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |
| 30838-128 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |
| 30838-130 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |
| 30838-132 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |
| 30838-134 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |
| 30838-136 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |
| 30838-141 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |
| 30838-148 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 261.8 mm | Alluminio |
| 30847-480 | Conductive | No | | No | 395.1 mm | Alluminio |
| 30847-482 | Conductive | No | | No | 395.1 mm | Alluminio |
| 30847-484 | Conductive | No | | No | 395.1 mm | Alluminio |
| 30847-556 | Conductive | No | IEC 60297-3- 101, IEEE 1101.1/10 | No | 395.1 mm | Alluminio |

| Table 3/3 | | | | | | | |
|-----------------|--------------|-------------------------------|-----------|----------------|--|--|--|
| Numero catalogo | Product Type | Tipo | Larghezza | Certificazioni | | | |
| 30838-123 | Front Panel | Front Panel without Handle | 426.4 mm | RoHS | | | |

| Numero catalogo | Product Type | Tipo | Larghezza | Certificazioni |
|-----------------|--------------|-------------------------------|-----------|----------------|
| 30838-204 | Front Panel | Front Panel without Handle | 426.4 mm | RoHS |
| 30847-465 | Front Panel | Front Panel without Handle | 426.4 mm | RoHS |
| 30847-469 | Front Panel | Front Panel without Handle | 426.4 mm | |
| 30847-461 | Front Panel | Front Panel without Handle | 426.4 mm | RoHS |
| 30838-081 | Front Panel | Front Panel without Handle | 213 mm | RoHS |
| 30838-102 | Front Panel | Front Panel without Handle | 319.7 mm | RoHS |
| 30838-162 | Front Panel | Front Panel without Handle | 213 mm | RoHS |
| 30838-183 | Front Panel | Front Panel without Handle | 319.7 mm | RoHS |
| 30847-459 | Front Panel | Front Panel without Handle | 213 mm | |
| 30847-460 | Front Panel | Front Panel without Handle | 319.7 mm | |
| 30847-463 | Front Panel | Front Panel without Handle | 213 mm | RoHS |
| 30847-464 | Front Panel | Front Panel without Handle | 319.7 mm | RoHS |
| 30847-467 | Front Panel | Front Panel without Handle | 213 mm | |
| 30847-468 | Front Panel | Front Panel without Handle | 319.7 mm | |
| 30847-458 | Front Panel | Front Panel without Handle | 141.9 mm | |
| 30847-470 | Front Panel | Front Panel without Handle | 9.8 mm | RoHS |
| 30838-067 | Front Panel | Front Panel without Handle | 141.9 mm | RoHS |
| 30838-043 | Front Panel | Front Panel without Handle | 20 mm | RoHS |

| Numero catalogo | Product Type | Tipo | Larghezza | Certificazioni |
|-----------------|--------------|-------------------------------|-----------|----------------|
| 30838-044 | Front Panel | Front Panel without Handle | 25 mm | RoHS |
| 30838-045 | Front Panel | Front Panel without Handle | 30.1 mm | RoHS |
| 30838-046 | Front Panel | Front Panel without Handle | 35.2 mm | RoHS |
| 30838-047 | Front Panel | Front Panel without Handle | 40.3 mm | RoHS |
| 30838-049 | Front Panel | Front Panel without Handle | 50.5 mm | RoHS |
| 30838-051 | Front Panel | Front Panel without Handle | 60.6 mm | RoHS |
| 30838-053 | Front Panel | Front Panel without Handle | 70.8 mm | RoHS |
| 30838-055 | Front Panel | Front Panel without Handle | 80.9 mm | RoHS |
| 30838-060 | Front Panel | Front Panel without Handle | 106.3 mm | RoHS |
| 30847-471 | Front Panel | Front Panel without Handle | 14.9 mm | RoHS |
| 30847-476 | Front Panel | Front Panel without Handle | 20 mm | RoHS |
| 30847-462 | Front Panel | Front Panel without Handle | 141.9 mm | |
| 30838-124 | Front Panel | Front Panel without Handle | 20 mm | RoHS |
| 30847-466 | Front Panel | Front Panel without Handle | 141.9 mm | |
| 30838-125 | Front Panel | Front Panel without Handle | 25 mm | RoHS |
| 30838-126 | Front Panel | Front Panel without Handle | 30.1 mm | RoHS |
| 30838-127 | Front Panel | Front Panel without Handle | 35.2 mm | RoHS |
| 30838-128 | Front Panel | Front Panel without Handle | 40.3 mm | RoHS |

| Numero catalogo | Product Type | Tipo | Larghezza | Certificazioni |
|-----------------|--------------|-------------------------------|-----------|----------------|
| 30838-130 | Front Panel | Front Panel without Handle | 50.5 mm | RoHS |
| 30838-132 | Front Panel | Front Panel without Handle | 60.6 mm | RoHS |
| 30838-134 | Front Panel | Front Panel without Handle | 70.8 mm | RoHS |
| 30838-136 | Front Panel | Front Panel without Handle | 80.9 mm | RoHS |
| 30838-141 | Front Panel | Front Panel without Handle | 106.3 mm | RoHS |
| 30838-148 | Front Panel | Front Panel without Handle | 141.9 mm | RoHS |
| 30847-480 | Front Panel | Front Panel without Handle | 40.3 mm | RoHS |
| 30847-482 | Front Panel | Front Panel without Handle | 50.5 mm | RoHS |
| 30847-484 | Front Panel | Front Panel without Handle | 60.6 mm | RoHS |
| 30847-556 | Front Panel | Front Panel without Handle | 426.4 mm | RoHS |

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE